





Systems Components



Technical Information

Condumax CLS21 and CLS21D

Conductivity sensors, analog or digital with Memosens technology Cell constant $k=1\ \mbox{cm}^{-1}$



Application

Measurements in media of medium and high conductivities:

- Medium separation in medium conductivities (milk/water)
- Medium separation in high conductivities (alkaline solution/ water)
- Drinking water treatment
- Wastewater treatment

The cell constant of the sensor is $k = 1 \text{ cm}^{-1}$. The measuring range reaches from 10 µS/cm to 20 mS/cm.

Sensors with a temperature sensor are used together with conductivity transmitters equipped with automatic temperature compensation:

- Liquiline CM442 / CM444 / CM448 (CLS21D only)
- Liquiline CM42
- Liquiline CM14 (CLS21D only)
- Mycom CLM153
- Liquisys CLM223/253

For measurement of resistivity, $M\Omega \boldsymbol{\cdot}$ cm measuring ranges are available in the menus of these transmitters.

Your benefits

- Various designs guarantee optimum adaptation to the process conditions and methods of installation
- Installation in pipes or flow chambers
- Compact design
- Available with plug-in head or fixed cable
- High chemical, thermal and mechanical stability
- IP 65 (with four-pole plug-in head) / IP 67 (with fixed cable) / IP 68 (with Memosens plug-in head)
- Quality certificate with statement of the individual cell constant

Further benefits offered by Memosens technology

- Maximum process safety through contactless inductive signal transmission
- Data safety through digital data transmission
- Easy handling thanks to storage of sensor-specific data in the sensor
- Predictive maintenance possible thanks to registration of sensor load data in the sensor



TI00085C/07/EN/13.12 71195954

Measuring principle Conductive measurement of conductivity The conductivity of liquids is measured with the AC following measurement setup: Two electrodes are immersed in the medium. An AC voltage is applied to these electrodes which generates a current in the medium. The electric resistance or its reciprocal value, the conductance G, is calculated according to Ohm's law. The specific conductivity κ is determined using the cell constant k that is dependent on the sensor geometry. a0003416 Conductive measurement of conductivity AC Power supply Current meter U Voltage meter General properties Electrodes The sensor has two coaxial electrodes made of graphite for a large measuring range. The graphite guarantees high chemical stability and low polarization effects. Temperature compensation A temperature sensor is integrated to measure the medium temperature. Durability - The sensor is pressure-proof up to 16 bar at 20 $^{\circ}$ C (232 psi at 68 $^{\circ}$ F). - It can be applied with temperatures of up to 135 °C at 2.5 bar (275 °F at 36.3 psi). Communication and data Digital sensors are able to store the following system data in the sensor: processing with CLS21D Manufacturing data – Serial number - Order code Date of manufacture Calibration data - Calibration date - Cell constant - Change in cell constant - Number of calibrations - Serial number of the transmitter used for the last calibration Application data - Temperature application range - Conductivity application range - Date of first commissioning - Maximum temperature value - Operating hours at high temperatures

Function and system design

Dependability with CLS21D

Reliability

The Memosens technology digitalizes the measured values in the sensor and transfers them to the transmitter contactlessly and free from interference potential. The result:

- An automatic error message is generated if the sensor fails or the connection between sensor and transmitter is interrupted.
- The availability of the measuring point is dramatically increased by immediate error detection.

Maintainability

Sensors with Memosens technology have integrated electronics that allow for saving calibration data and further information such as total hours of operation and operating hours under extreme measuring conditions. When the sensor is connected, the calibration data are automatically transferred to the transmitter and used to calculate the current measured value. Storing the calibration data in the sensor allows for calibration and adjustment away from the measuring point. The result:

- Sensors can be calibrated unter optimum external conditions in the measuring lab. Wind and weather do neither affect the calibration quality nor the operator.
- The measuring point availability is dramatically increased by the quick and easy replacement of precalibrated sensors.
- Maintenance intervals can be defined based on all stored sensor load and calibration data and predictive maintenance is possible.
- The sensor history can be documented on external data carriers and evaluation programs at any time. Thus, the current application of the sensors can be made to depend on their previous history.

Integrity

The inductive and non-contacting measured value transmission of Memosens guarantees maximum process safety and offers the following benefits:

- All problems caused by moisture are eliminated.
 - The plug-in connection is free from corrosion.
 - Measured value distortion from moisture is not possible.
 - The plug-in system can even be connected under water.
- The transmitter is galvanically decoupled from the medium.
- EMC safety is guaranteed by screening measures for the digital measured value transmission.

Measuring system

A complete measuring system comprises:

- a CLS21 or CLS21D conductivity sensor
- a transmitter, e.g. Liquiline CM42
- a measuring cable, e.g. CYK71 or CYK10 Memosens data cable



Measuring system example

- Liquiline CM42 transmitter
- CYK10 Memosens data cable 3
- Condumax CLS21D sensor

	Input				
Measured variable	ConductivityTemperature				
Measuring range	Conductivity CLS21D and CLS21 valid in the specified tempe specified measuring accura	(referenced to water at 25 °C (77 °F)) 10 μS/cm to 20 mS/cm erature range .cy up to 100 °C (212 °F)			
	Temperature CLS21D CLS21 specified measuring accura	-20 to 100 °C (-4 to 212 °F) -20 to 135 °C (-4 to 275 °F) acy up to 100 °C (212 °F)			
Cell constant	$k = 1.0 \text{ cm}^{-1}$, nominal				
Temperature compensation	CLS21D NTC CLS21 Pt 100 (class A acc. to IEC	60751)			

Power supply

Electrical connection

CLS15

The sensor is connected to the transmitter using the measuring cable CYK71 or the fixed cable.



Measuring cable, CYK71 or fixed cable

CLS15D

The sensor is connected to the transmitter via the measuring cable CYK10.



Measuring cable CYK10

Performance characteristics, in general

Measured error Each individual sensor is factory measured in a solution of approx. 5 mS/cm on a reference measuring system referred to NIST or DKD. The accurate cell constant is entered in the supplied quality certificate. The maximum measured error in cell constant determination is 1.0 %.

Performance characteristics, CLS15D only

Conductivity response time	$t_{95} \leq 3 s$
Temperature response time	$t_{90} \le 296 \ s$
Maximum measured error	5 % of the measured value
Repeatability	0.2 % of the measured value

Installation

Installation conditions

The sensors are mounted directly via the process connection. Optionally, they can be installed in flow assemblies.





Installation in the CLA751 flow assembly

Installation in the CLA752 flow assembly

a0003418

a0003422



For installation of sensors with G1 thread in tanks, the CLA111 immersion and process assembly is available (see Accessories).

Dipfit CLA111, mounting versions A, B and D

The measuring surfaces must be completely immersed in the medium during operation.

Environment

Ambient temperature	-20 to +60 °C (-4 to +140 °F)			
Storage temperature	-25 to +80 °C (-10 to +180 °F)			
Humidity	5 to 95%			
Protection degree	CLS21 Fixed cable version Plug-in head version CLS21D	IP 67 / NEMA 6 IP 65 / NEMA 4X IP 68 / NEMA Type 6P (10 m water column, 25 °C, 168 h)		

	Process			
Process temperature	-20 to +135 °C (-4 to 275 °F) at 2.5 bar (36 psi)			
	The maximum temperature for communication between Memosens sensors and the transmitter is 130 °C (266 °F).			
Process pressure	16 bar (230 psi) at 20 °C (68 °F)			
Pressure/temperature load curves	$p [psi] p [bar]$ $250_{232} - 16$ $250_{232} - 16$ 12 150 100 12 150 4 $-50_{63} - 2.5$ 0 -20 0 -20 0 -20 0 -20 0 -20 0 -20 0 -20 0 -20			

Mechanical pressure-temperature stability of

Mechanical construction







Dimensions of fixed cable version with Clamp 2"



Dimensions of fixed cable version with SMS



Dimensions of plug-in head version with dairy fitting

Dimensions of plug-in head version with SMS

Dimensions of CLS21D



Material

Weight

graphite Electrodes: Sensor shaft:

polyether sulfone (PES-GF20)

Thermal conductivity socket for temperature

sensor:

titanium 3.7035

Process connections

CLS21

Fixed cable version: Thread NPT 1" Clamp 2" acc. to ISO 2852 SMS DN 38 (1½") Plug-in head version: Thread G 1 Clamp 2" acc. to ISO 2852 Dairy fitting DN 25 or DN 40 acc. to DIN 11851 SMS DN 38 (1½")

CLS21D

Thread G1 Thread NPT 1" Clamp 2" acc. to ISO 2852 Dairy fitting DN 25 acc. to DIN 11851

Clamp connection:

Sensors with clamp connections can be fixed using sheet metal brackets or solid brackets. Sheet metal brackets have a lower dimensional stability, uneven bearing surfaces causing point loads and sometimes sharp edges that can damage the clamp.

We strongly recommend to always use solid brackets because of their higher dimensional stability. Solid brackets may be applied over the total pressure-temperature range (see temperature-pressure load curve).

Certificates and approvals

Ex approval	 CLS21 ATEX II 1G Ex ia IIC T3 / T4 / T6 FM/CSA IS/NI CL I Div. 1 & 2 GP A - D in combination with the Liquiline CM42 and Mycom CLM153 transmitters 				
	CLS21D-**G ■ ATEX /NEPSI II 1G Ex ia IIC T3 / T4 / T6, IECEx Ex ia IIC T6 Ga				
	CLS21D-**O ■ FM/CSA IS/NI CL I Div. 1 & 2 GP A - D in combination with the Liquiline CM42 transmitter				
	CLS21D-**V ■ ATEX/NEPSI II 3G Ex nL IIC T3 / T4 / T6 for the use in Zone 2 with transmitter Liquiline CM42-KV***				
	ATEX and FM/CSA versions of digital sensors with Memosens technology are indicated by an orange-red ring in the plug-in head.				

Quality certificate

With statement of the individual cell constant

Ordering information

Product pages	www.products.endress.com/cls21 www.products.endress.com/cls21d		
Product configurator	 You can choose from the following options on the product page located on the right: Product page function :: Add to product list :: Price & order information :: Compare this product :: Configure this product 		
	2. Click "Configure this product".		
	3. The configurator opens in a separate window. You can now configure your device and receive the complete order code that applies for the device.		
	4. Afterwards, export the order code as a PDF or Excel file. To do so, click the appropriate button at the top of the page.		

Product structure Condumax CLS21

The following product structure represents the status of printing. You can create a complete and valid order code on the Internet using the configurator tool.

	Measuring range and cell constant					
	С	Measu	Measuring range: $10.0 \ \mu S \dots 20 \ m S/cm \ (k = 1)$			
		Proce	cess connection and materials			
		1E	Thread	Thread G 1, PES (plug-in head version only)		
		1N	Thread	Thread NPT 1", PES (fixed-cable version only)		
		2A	Dairy f	Dairy fitting DN 25, DIN 11851, PES (plug-in head version only)		
		2B	Dairy f	Dairy fitting DN 40, DIN 11851, PES (plug-in head version only)		
		2C	Process	s connec	tion SMS DN 38, PES	
		3B	Clamp	Clamp 2", PES		
			Measuring cable connection			
			2	2 with 5 m / 16.41 ft fixed cable		
			3 with 10 m $/$ 32.81 ft fixed cable			
			4 four-pole DIN connector with Pg 9, DIN 43650-A			
				Temperature sensor		
				А	Integrated Pt 100 temperature sensor	
				D	No temperature sensor	
CLS21-					complete order code	

Product structure

Condumax CLS21D

	Measuring range and cell constant					
	С	Measu	Measuring range: 10.0 μ S to 20 mS/cm (k = 1)			
	L	PWIS-	PWIS-free for measuring range 10.0 $\mu S/cm$ to 20 mS/cm $(k=1)$			
		Proce	ocess connection and materials			
		1E	Thread	1 G 1, PES		
		1N	Thread	1 NPT 1", PES		
		2A	Dairy f	Dairy fitting DN 25, DIN 11851, PES		
		3B	Clamp	Clamp 2", PES		
			Approval			
			G	ATEX/NEPSI II 1G Ex ia IIC T3/T4/T6 Ga, IECEx Ex ia IIC T6 Ga		
			0	FM/CSA IS/NI Cl I Div. 1 & 2 GP A - D		
			V	ATEX/NEPSI II 3G Ex nL IIC T3/T4/T6		
			1	Non-hazardous areas		
CLS21D-				complete order code		

Accessories

In the following sections, you find the accessories available at the time of issue of this documentation. For information on accessories that are not listed here, please contact your local service or sales center.

Connection	Measuring cables					
	 CYK71 measuring cable Non-terminated cable for the connection of sensors (e.g. conductivity sensors) or the extension of sensor cables Sold by the meter, order numbers: non-Ex version, black: 50085333 Ex version, blue: 50085673 CYK10 Memosens data cable For digital sensors with Memosens technology pH, redox, oxygen (amperometric), chlorine, conductivity (conductive) Ordering as per product structure (-> online Configurator, www.products.endress.com/cyk10) 					
	Junction boxes					
	Junction box VBM ■ For cable extension ■ 10 terminals ■ Cable entries: 2 x Pg 13.5 or 2 x NPT ½" ■ Material: aluminum ■ Ingress protection: IP 65 (≅ NEMA 4X) ■ Order numbers: — cable entries Pg 13.5: 50003987 — cable entries NPT ½": 51500177					
	Junction box VBM-Ex ■ For cable extension in hazardous areas ■ 10 terminals (blue) ■ Cable entries: 2 x Pg 13.5 ■ Material: aluminum ■ Ingress protection: IP 65 (≅ NEMA 4X) ■ Order no.: 50003991					
Calibration solutions	 Precision solutions referred to SRM (Standard Reference Material) of NIST for qualified calibration of conductivity measuring systems according to ISO, with temperature table CLY11-A 74 μS/cm (reference temperature 25 °C (77 °F)), 500 ml (16.9 fl.oz) order no. 50081902 CLY11-B 149.6 μS/cm (reference temperature 25 °C (77 °F)), 500 ml (16.9 fl.oz) order no. 50081903 CLY11-C 1.406 mS/cm (reference temperature 25 °C (77 °F)), 500 ml (16.9 fl.oz) order no. 50081904 CLY11-D 12.64 mS/cm (reference temperature 25 °C (77 °F)), 500 ml (16.9 fl.oz) order no. 50081905 					
	For further information on calibration solutions see Technical Information TI00162C/07/EN.					

Assemblies

Dipfit CLA111

- Immersion assembly for open and closed tanks with flange DN 100
- Ordering acc. to product structure, -> online configurator: www.products.endress.com/cla111
- Technical Information TI00135C/07/EN

CLA751 flow assembly

- For installation of conductivity sensors with G 1 thread.
- Inlet (bottom) and outlet (lateral) DN 20 with union nuts G 1.
- Stainless steel 1.4571 (AISI 316Ti)
- Max. temperature: 160 °C (320 °F)
- Max. pressure: 12 bar (174 psi)
- Order no.: 50004201



CLA751 flow assembly

CLA752 flow assembly

- For installation of conductivity sensors with G 1 thread
- \blacksquare Inlet (lateral) and outlet (lateral) DN 20 with G $\frac{1}{2}$ internal thread
- Polypropylene (PP)
- Max. temperature: 90 °C (194 °F)
- Max. pressure: 6 bar (87 psi)
- Order no.: 50033772



CLA752 flow assembly

Instruments International

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel.+41 61 715 81 00 Fax+41 61 715 25 00 www.endress.com info@ii.endress.com

