## 315 Subject to modification in technic and design. Errors and omissions excepte

## Absolute encoders - analog

## Encoder with cable-pull Magnetic sensing, resolution 12 bit

## BMMS K23 / K50 analog / cable-pull - MAGRES



BMMS K50 analog with connector M12

## **Features**

- Encoder with cable-pull
- Magnetic sensing method
- Resolution: 12 bit
- Interface analog 0...10 V / 0.5...4.5 V / 4...20 mA
- Measuring length 2300 mm or 5000 mm
- Removable cabs for water outlet
- Teach inputs
- Extremely flat design
- Extremely light thanks to housing of plastic and aluminum

Technical data - electrica	l ratings	
Voltage supply	830 VDC	
Reverse polarity protection	Yes	
Short-circuit proof	Yes	
Consumption typ.	35 mA (24 VDC, w/o load)	
Initializing time	≤500 ms after power on	
Response time	<1 ms	
Interface analog	010 V / 0.54.5 V / 420 mA Resolution: 12 bit	
Function	Linear position feedback	
Sensing method	Magnetic	
Interference immunity	DIN EN 61000-6-2	
Emitted interference	DIN EN 61000-6-4	
Programmable parameters	Measuring range teachable	
Diagnostic functions	Self-diagnosis Reading back voltage output	
Factory setting	Entire measuring range Min. output at 0 m Max. output at 2.3 m, 5 m	
BMMS K23		
Linearity	0.17 % of whole measuring range	
Repeatability typ.	2 mm	
BMMS K50		
Linearity	0.45 % of whole measuring range	
Repeatability typ.	4 mm	

Technical data - mechan	ical decian
	•
Protection DIN EN 60529	IP 65 (encoder)
Materials	Encoder housing: aluminium Cable-pull housing: PA6 GF30 Cable: Stainless steel cable sheathed with polyamide
Operating temperature	-40+85 °C
Service life	Type >500000 strokes
Cable acceleration	≤50 m/s²
Cable diameter	0.45 mm
Pull-in force	>3 N
Pull-out force	≤9 N
Relative humidity	95 % temporary condensing
Resistance	DIN EN 60068-2-6 Vibration 10 g, 10-2000 Hz DIN EN 60068-2-27 Shock 50 g, 11 ms
Weight approx.	400 g
Connection	Connector M12, 5-pin Connector M12, 8-pin Cable 2 m
Bending radius	Cable: >55 mm
Special characteristics	Coated electronic
Instruction	Please consider the assembly instructions
BMMS K23	
Measuring length	2300 mm
BMMS K50	
Measuring length	5000 mm

# 23/12/2015 Subject to modification in technic and design. Errors and omissions excepted.

## Absolute encoders - analog

Encoder with cable-pull Magnetic sensing, resolution 12 bit

## BMMS K23 / K50 analog / cable-pull - MAGRES

Part number				
Measuring length r	nax. 2.3 m	Measuring length max. 5 m		
BMMS K235N24	12/16 00	BMMS K505N24 12/16 00		
	Connection  5 Cable 2 m, radial  M 2 x connector M12, 5-pin, radial (redundant version)  N Connector M12, 5-pin, radial (not redundant version)  Q Connector M12, 8-pin, radial	Connection 5 Cable 2 m, radial M 2 x connector M12, 5-pin, radial (redundant version) N Connector M12, 5-pin, radial (not redundant version) Q Connector M12, 8-pin, radial		
	Resolution 12/16 12/16 bit single-/multiturn	Resolution 12/16 12/16 bit single-/multiturn		
L E		Analog signals U 010 VDC 5 0.54.5 VDC		
\ <del>7</del> \ -	7 0.54.5 VDC redundant	V 420 mA 7 0.54.5 VDC redundant Y 010 VDC redundant Z 420 mA redundant		

_	
Access	Orine
ACCESS	OLICS

Connectors and cables				
10153968	Female connector M12, 5-pin, straight, without cable			
11046266	Female connector M12, 5-pin, straight, 5 m cable			
10156842	Cable with male/female M12, 5-pin, angled, A-coded, 5 m			
11144306	Cable with male/female M12, 5-pin, straight, A-coded, 5 m			
10146775	Female connector M12, 8-pin, straight, without cable			

## Absolute encoders - analog

Encoder with cable-pull Magnetic sensing, resolution 12 bit

## BMMS K23 / K50 analog / cable-pull - MAGRES

Terminal significance				
+Vs	Cable-pull encoder supply voltage. (Redundant configuration provides decoupled dual voltage supply (+Vs1/+Vs2) separated by diodes.			
0 V	Cable-pull encoder ground connection relating to +Vs.			
lout	Current output. Load: <500 Ω			
Uout	Voltage output. Current output: max. 10 mA Load resistor: >1 k $\Omega$ between Uout / 0 V			
Set	Teach input. Resting state: Low Level High: >0.7 x +Vs Level Low: <0.3 x +Vs Pull-Down resistor: 10 $k\Omega$			
DV/Status	Diagnostic output/Teach output.  R <sub>L</sub> - Vs: High: >(+Vs -1.0 V) Low: <3.0 V  R <sub>L</sub> - GND: High: >(+Vs -3.0 V) Low: <1.0 V  I <sub>Lmax</sub> = 10 mA  Upon any short-time disturbance, DV will go on Low for 1 second.			
Drain	Encoder housing.			

### **Teach process**

The teaching functionality will be disabled 5 minutes after cable-pull encoder power on. Time begins to start anew after each teaching operation.

- Set input on HIGH for 6 seconds. DV/ status output reflects the reverted input and will start oscillating after 5 seconds. Now set input on LOW.
- Get cable-pull encoder in position 1 intended for voltage output 1/current 1.
- Set input on HIGH for 1 second. DV/ status output will switch to LOW for 3 seconds and then start oscillating.
- 4. Get cable-pull encoder in position 2 intended for voltage output 2/current 2.
- Set input on HIGH for 1 second. DV/Status output will switch to HIGH for 3 seconds and then shortly oscillate to signal that the teaching operation has been completed.


In the event of one out of both taught limits being beyond the sensing range or too close to each other, the DV/status output will oscillate shortly. There is no teaching of sensing range. The operation must be repeated under consideration of minimum teaching limit and sensing range.


## Set / restore default

Set input on HIGH for 16 seconds. (After 5 seconds, the DV/status output will start oscillating while restoring default in second 15).

Note: The cable pull has to be completely drawn in.

## **Behavior**







# 23/12/2015 Subject to modification in technic and design. Errors and omissions excepted.

## Absolute encoders - analog

Encoder with cable-pull Magnetic sensing, resolution 12 bit

## BMMS K23 / K50 analog / cable-pull - MAGRES

Terminal as	ssignment					
Cable for connection	on reference -	5		Cable redu for connection	ndant on reference -5	
Core color	Analog signa U/5	als V	W	Core color	Analog signa Y/7	ls Z
white	0 V	0 V	0 V	white	0 V	0 V
brown	+Vs	+Vs	+Vs	brown	+Vs 1	+Vs 1
green	d.u.	lout	lout	green	Uout 1	lout 1
yellow	Uout	d.u.	Uout	yellow	Uout 2	lout 2
grey	Set	Set	Set	grey	Set 1	Set 1
oink	DV/Status	DV/Status	DV/Status	pink	DV/Status 1	DV/Status 1
Screen	connected to	housing		blue	Set 2	Set 2
Cable data	6 x 0.14 mm	2		red	DV/Status 2	DV/Status 2
				black	0 V	0 V
				violet	+Vs 2	+Vs 2
				Screen	connected to	housing
				Cable data	10 x 0.14 mm	1 <sup>2</sup>

## Connector M12, 5-pin for connection reference -N

Connector	Analog signals			
	U/5	V	W	
Pin 1	0 V	0 V	0 V	
Pin 2	+Vs	+Vs	+Vs	
Pin 3	d.u.	lout	lout	
Pin 4	Uout	d.u.	Uout	
Pin 5	Set	Set	Set	



## Connector M12, redundant, 2 x 5-pin

for connection reference -M

Connector	Connector 1	Connector 2
Pin 1	0 V	0 V
Pin 2	+Vs 1	+Vs 2
Pin 3	Uout 1 (Y/7) lout 1 (Z)	Uout 2 (Y/7) lout 2 (Z)
Pin 4	DV/Status 1	DV/Status 2
Pin 5	Set 1	Set 2



## Absolute encoders - analog


Encoder with cable-pull

Magnetic sensing, resolution 12 bit


## BMMS K23 / K50 analog / cable-pull - MAGRES

## **Dimensions**

## BMMS K23 / K50 cable radial



### BMMS K23 / K50 connector M12



## BMMS K23 / K50 connector 2 x M12

